



Spectra Unit _ Know light, better

Model No: CLSK-05V

Description:

The CLSK-05V unit has been specifically designed to allow the observer to compare the spectra of different light source, visually. The large format transmission grating frame will allow the user to view the spectrum of the currently turned on light source in detail. For higher spectral line separation, second order spectrum can be observed. It is recommended to operate the instrument in absence of direct ambient light. The extensible dark background enables the observation experience even without a proper dark room. The spectra unit is crisper and brighter, making it much easier know light the fully integrated power supply uses modern technology that lowers your running costs. It is mechanically and electrically compatible and is supplied with all the relevant cables and connectors to ensure a fast plug and play installation.

Uses:

- Understand various types of spectra.
- Study source color composition.
- Quick spectrum comparison.

Grating:

- Grating, 1000 lines/mm.
- Framed for easy handling.
- With 5.5"x2.5" grating area.

Sources:

- Robust 1'x3' aluminum frame.
- Extended black background.
- Individual switching.
- Custom combinations available.

Remote and Pate:


- Remote
- Glass plate

Power:

- Use power entry socket
- Input Ac power 230V Ac 50/60HZ
- Standard 3 pin power cable.

List Accessories:

- Remote :1 No
- Power cable 1.5metr : 1 No
- Glass: 1 No
- M4 Screw with rawlplug sizes : 7 Nos






Installation instructions of Spectra Unit

Spectra Unit easy to install of wall mount as showing picture and below Installation instructions.

Spectra unit mount using mostly basic tools. Even though it's a simple process, mounting an spectra unit on a wall isn't a 1-person job. You typically need 1 or 2 people to hold the unit and one person to attach the mount to the wall. Set aside about an hour to complete the process, once you have all of your tools and the mount on hand.

Tools needed

You will need the following tools to assemble your new TV wall mount:



Steap 1: Marck the M4 size 6 whole (Top side 3 ot nbottom side 3) as per the your mouting locationns.

Steap 2: Use M4 Screw and rawlplug sizes for mounting.

Step 3: Determine the placement of spectra unit on the wall. Make sure that nothing obstructs the view of your spectra unit when you determine where on the wall to place your mount.

Step 4: set the sliding frame and mount center screw. For sliding black frame locking purpose.



WARRANTY CERTIFICATE

Please complete the following details and retain with the ordinal purchase docket.

Owner's Name:

Address:

State: _____ Post Code:

Product Details:

Model No: _____ Serial Number:

Date of Purchase: _____ Invoice No:

Warranty and Support

Due to the use of top-quality components and solid design the skillful product's range of replacement Spectra unit have a one-year manufacturer's warranty and accessories three month.

This is backed by our skillful Pune office based after sales service to give you complete peace of mind on your purchase.

Stamp & Sing .

Skillful Technologies .